

Batten Lights

Features

- High performance LED
- Retrofittable replacement solution for T8 fluorescent fittings used in commercial applications
- Colour temperature CCT3 (3000K,4000K,6500K) selectable via internal 3-way switch
- 120° Beam Angle
- ENEC approved driver
- Voltage: 220-240V
- Wire Fittings Supplied
- IP20 rating, suitable for indoor use
- Steel body, Polycarbonate body and diffuser
- 20 mm cut-out
- IP20 rating
- Suitable for Indoor Use

RS PRO Power Selectable CCT3 LED Batten Lights - Twin Batten with Emergency

RS Stock No: 231-8159, 231-8163, 231-8167



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Batten Lights

Product Description

Introducing the RS PRO range of LED CCT3 professional batten lights. A selection of high-performance LED luminaires perfect for use in commercial buildings. These energy-efficient, LED lights are the ideal retrofittable replacement solution for T8 fluorescent fittings. Upon inspection, made from steel with a polycarbonate diffuser, include an Internal selector switch and wire fittings.

Technical Specifications

Voltage:	220-240V
Frequency	50-60 Hz
Power Factor	>0.9
Colour Temperature	3000K, 4000K & 6500K
Construction	Steel Body & polycarbonate diffuser
Beam Angle	120°
IP Rating	IP20
Dimmable	No
Light Source	Non-Replaceable LED
Lifespan	50,000hrs
Luminous Efficacy	100 lm/W+
ENEC approved driver	Yes
Standards	IEC61347, EN 61347, EN 62384, EN 60598
Non-Corrosive	Yes

Variants

RS Stock no:	Type	Wattage	Colour Temperature	Length
231-8159	Twin Batten	40 W	3000K,4000K,6500K	L.1200 mm
231-8163	Twin Batten	60 W	3000K,4000K,6500K	L.1500 mm
231-8167	Twin Batten	80 W	3000K,4000K,6500K	L.1800 mm

Batten Lights

