



PRODUCT-DETAILS

OTP90A4U

OTP90A4U Safety switch



General Information

Extended Product Type	OTP90A4U
Product ID	1SCA022430R2030
EAN	6417019135533
Catalog Description	OTP90A4U Safety switch

Long Description	<p>Safety switch, 4-p. 415V AC23 90A, 45kW. Mounted auxiliary contact: 1NO0NC. Plastic enclosure. IP65. RedYellow Selector handle. Interlocked cover. Defeatable interlocking.</p> <p>The enclosure in the OTP series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. Cable entry holes to be made by the installer. The handle is padlockable and made for three padlocks. The interlocking can be by-passed, for thermographing etc. The switch is made for 5 wire system, and have a fixed neutral terminal and PE terminal.</p>
------------------	---

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201
RoHS Declaration	1SCC340075D0201

RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340002M0012
Mechanical Drawings	OTPK402014SBL.stp

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Last Ordering Date	2026-08-31 All Countries
Replacement Product ID (NEW)	OTP80GA4M
Country or Territory of Origin	Finland

Dimensions

Product Net Width	200 mm
Product Net Height	400 mm
Product Net Depth / Length	140 mm
Product Net Weight	2.2 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	213 mm
Package Level 1 Depth / Length	417 mm
Package Level 1 Height	197 mm
Package Level 1 Gross Weight	2.4 kg
Package Level 1 EAN	6417019135533

Technical

Cable Cross-Section	10 ... 70 mm ²
Cable Entry Position	Top and/or Bottom
Cable Outlets Per Side	Blank /Blank
Color	RAL7035
Connecting Capacity	Screw Clamp 10 ... 70 mm ²

Main Circuit	Screw Clamp / PE Terminal 4pc,10 ... 70 mm ²
Conventional Thermal Current (I _{the})	Fully Enclosed 125 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Plastic
Handle Color	Red / Yellow
Handle Type	Selector handle
Impact Resistance Rating	Housing IK08
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	1 NO, 0 NC
Neutral Type	Fixed and Switchable Neutral
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Poles	4P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 6.3 W
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A (I _e)	(380 ... 415 V) 125 A (500 V) 125 A (690 V) 125 A
Rated Operational Current AC-23A (I _e)	(380 ... 415 V) 90 A (500 V) 70 A (690 V) 50 A
Rated Operational Power AC-23A (P _e)	(380 ... 415 V) 45 kW (500 V) 45 kW (690 V) 45 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I _{cm})	(690 V AC) 3.6 kA
Rated Short-time Withstand Current Low Voltage (I _{cw})	for 1 s 2.5 kA
Recommended Screw Driver	Main Circuit Hexagon 4
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 6 N·m
Wire Stripping Length	20 mm

Technical UL/CSA

Wire Stripping Length	20 mm
Recommended Screw Driver	Main Circuit Hexagon 4
Tightening Torque	Main Circuit 6 N·m

Certificates and Declarations

BV Certificate	1SCC340018D0204
Declaration of Conformity - CE	1SCC340003D2704
DNV GL Certificate	1SCC340045D0203

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnecter (low voltage)
ETIM 10	EC000216 - Switch disconnecter (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

