

Blower LXT®

DUB186

18V • 68 m/s • 3.2 m³/min

Compact blower with long tube for versatile use

With a handy-sized blower, you blow small debris and leaves. The blower is also suitable for cleaning casting molds, machines or work sites. The blower has infinitely variable blowing volume control and comes with a long blowing tube. The maximum air flow of the machine is 68 m/s and the amount of air is 3.2 m³/min.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
No load speed	0 - 18000 min ⁻¹
Max. Air Velocity	68 m/s
Blowing force	2,5 N
Air volume	0 - 3,2 m³/min
Continuous Use 18V / 5.0 Ah Battery	130 / 50 / 21 min
Sound Power Level (L _{WA})	92,4 dB(A)
Sound Pressure Level (L _{pA})	82,5 dB(A)
Noise Uncertainty (K Factor)	2,8 dB(A)
Tool weight with battery	1,6 - 2,1 kg
Product Dimensions (L x W x H):	861 x 156 x 210 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Continuous Use 18V / 3.0 Ah Battery	80 / 30 / 12 min

User benefits

- Variable speed
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makita.uk.com



Related products

Optional AC

123241-2 Dust Bag Assembly		123245-4 Nozzle Assembly	
123246-2 Nozzle Assembly 43 cm		191G09-6 Garden nozzle assembly set	
191M30-1 Brush Nozzle		191M32-7 Wiper Nozzle Set	
191M34-3 Flexible Hose Set			

Other

User manual

Parts drawing