



DCS397T2

54V 430mm Alligator Saw

Selling Proposition

- New 54V FLEXVOLT Li-Ion battery enables corded performance from a cordless tool.
- Ideal for cutting Class 12 clay blocks (Poroton),
- Durable high power Brushless motor for the toughest applications
- Two long life and durable saw blades running in opposite directions so the material will not move while cutting
- Dust sealed gearcase and bearings for increased durability
- Aluminium gearcase housing for lower weight and excellent durability

Standard Equipment

- TCT Class12, set of blades
- Hex key
- 2 x 54V FLEXVOLT batteries
- 1 x Battery Charger

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	
Battery chemistry	Li-Ion
Voltage	54 V
Battery	FLEXVOLT 6.0Ah
Power Output	
No Load Stroke Rate	2400 spm
Stroke Length	40 mm
Blade Length	43.0 cm