

Main

Range of product	Harmony
Product or component type	Digital display head
Mounting diameter	22 mm
Cap/operator or lens colour	Yellow
[Us] rated supply voltage	24 V DC





Complementary

Display type	7 segments LED + decimal point
Supply voltage limits	13...30 V
Net weight	0.02 kg

Environment

Product certifications	CSA[RETURN]UL
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	10 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	180 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to NF C 20-030
IP degree of protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Circularity Profile	No need of specific recycling operations