

Metric Size - TU TU1208R1-20

Datasheet

General series information

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

Standard specifications

Size	1208 (O.D. Ø12, I.D. Ø8)
Color	R1 (Red, Solid)
Roll Length	20 m
Reel Length	None
Suffix	None
Pressure medium	Air, Water
Maximum ambient temperature	60 °C / 40 °C for Water
Minimum ambient temperature	-20 °C (with no freezing) / 0 °C for Water
Number of pneumatic connections	2 pcs.
Max. operating pressure at 20 °C	0.8 MPa
Weight	1.550 Kg

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)