

VS-PPC-F1-SCRJ-MNNA-1RF - Panel-mount frame



1405374

<https://www.phoenixcontact.com/in/products/1405374>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



SC-RJ panel mounting frame, IP67, for push-pull interlocking, metal, with Freenet system, for rectangular mounting cutout, with seal and SC-RJ coupling (for POF, PCF, and GOF), without mounting screws

Commercial data

Item number	1405374
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABN
Product key	ABNODE
Catalog page	Page 356 (C-4-2015)
GTIN	4046356419925
Weight per piece (including packing)	35.6 g
Weight per piece (excluding packing)	35.6 g
Customs tariff number	85389099
Country of origin	DE

VS-PPC-F1-SCRJ-MNNA-1RF - Panel-mount frame



1405374

<https://www.phoenixcontact.com/in/products/1405374>

Technical data

Product properties

Product type	Panel-mount frame
Application	Freenet
Type	SC-RJ
Number of positions	2
Connection profile	SC-RJ
Type	SC-RJ
Cable outlet	straight

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties


Transmission medium	FO
---------------------	----

Connection data

Connection technology

Connection method	Push-Pull
-------------------	-----------

Dimensions

Dimensional drawing	
Width	22.2 mm
Height	42 mm

Mechanical characteristics

Ferrule diameter	2.50 mm
------------------	---------

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	nickel-plated

Cable/line

Resistance to oil	yes
Flame resistance	yes

FO cable

1405374

<https://www.phoenixcontact.com/in/products/1405374>

Number of fibers	2
Fiber	POF, PCF, GOF
Fiber type	GOF, PCF, POF
Transmission medium	FO

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67 (IP65/67)
	IP65/IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	0 °C ... 50 °C
Resistance to oil	yes

Standards and regulations

Flame resistance	yes
Resistance to oil	yes

Mounting

Mounting type	Panel mounting
---------------	----------------

VS-PPC-F1-SCRJ-MNNA-1RF - Panel-mount frame


1405374

<https://www.phoenixcontact.com/in/products/1405374>




Drawings

Exploded view



Dimensional drawing



Mounting cutout

VS-PPC-F1-SCRJ-MNNA-1RF - Panel-mount frame



1405374

<https://www.phoenixcontact.com/in/products/1405374>

Classifications

ECLASS

ECLASS-11.0	27440210
ECLASS-12.0	27440210
ECLASS-13.0	27440210

ETIM

ETIM 9.0	EC002310
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1405374

<https://www.phoenixcontact.com/in/products/1405374>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in