PRODUCT-DETAILS

Bypass PDU 16A PowerValue 11 RT

Bypass PDU 16A PowerValue 11 RT



General Information

Extended Product Type	Bypass PDU 16A PowerValue 11 RT
Product ID	4NWP101737R0001
ABB Type Designation	Bypass PDU 16A PowerValue 11 RT
EAN	7640169260773
Catalog Description	Bypass PDU 16A PowerValue 11 RT
Long Description	Manual service bypass with PDU for PowerValue 11RT 1-3 kVA

ABB EcoSolutions

Environmental Product Declaration - EPD	No certification needed

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD005611

© 2025 ABB. All rights reserved.

RoHS Declaration	4NWD005610
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	b4d68c02-53b4-4c8b-acf4-13b50687677d Switzerland
Simplified SCIP	75ea3240-4721-45ab-b144-1b06b2d96fb5 Belgium 86c14217-d891-4d58-bf7c-1d955d2e2cb0 Estonia b0a0336f-bef8-4dfd-981d-0825ef13bbef Greece b865f7d0-5e5d-40de-b9d2-1df574faa521 Hungary 6f61cc3c-0fa0-4ed0-b9db-ce4640881666 Germany 98abc58e-608d-4b83-9920-457c9c801e98 France b4703d4e-0212-4af6-a233-e2cff3a68eaf Sweden 914610a9-1b58-4cf9-b645-d89c66139324 Sweden 47a0b4be-3e94-4965-9ef8-9f2bc20dd73b Denmark d4ab57ef-30d5-4fb3-88b0-19fd3cfdd6e5 Bulgaria 37ed868f-d1e7-4254-9dc4-db3ce7badce7 Belgium 3b9343c2-e00a-445e-859d-1bfe6a80f488 Germany b24ef6c2-2124-404e-815f-a98a944ca8e8 Portugal 5d137a0a-8581-4192-802f-932344e86530 Norway 02361eda-32d9-4636-bb53-4be441ec27d3 Poland bd96fb9f-b107-4b24-b421-2e738fdf5e8b Finland c830f218-0139-4a05-8af1-6d1ac44c5271 Poland 75d44057-cf51-4c7e-9821-bb0f72149ea1 Germany f3c3fb2f-f4e7-444d-a386-ff8bd4b7feb9 Germany 1c033008-1eb2-43e3-ab23-fb7dcefc08e2 Spain d0e2e51b-6079-4382-8aec-4edb56cfd879 France c002da23-92c9-48e1-8300-bdde46e4511e Hungary fd89aeae-da68-4485-bbf8-50af5be04ac9 Poland e3ba8c12-2368-4875-95a0-f5963c614655 Czech Republic 37799602-7dfb-478b-908b-657b2677a36b Netherlands 67abe7cb-a504-4db7-ad38-dda6a9ded7e3 Germany 6038cec1-55c2-4ee3-839a-466e7e3f0c5c Croatia

Popular Downloads

Data Sheet, Technical Information	9AKK10103A5251
Instructions and Manuals	9AKK10103A5251

Environmental

Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85371092
E-Number (Finland)	8408576
E-Number (Norway)	6600755
Country or Territory of Origin	China

Dimensions

Product Net Width	395 mm
Product Net Height	78 mm
Product Net Depth / Length	88 mm
Product Net Weight	3.75 kg

© 2025 ABB. All rights reserved.

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	460 mm
Package Level 1 Height	170 mm
Package Level 1 Depth / Length	195 mm
Package Level 1 Gross Weight	3.8 kg
Package Level 1 EAN	7640169260773

Technical

Accessory Group	UPS Option
Accessory Type	Bypass
Current Rating	16 A
Frame Size	Undefined
Suitable For	PowerValue 11RT G2 1 kVA PowerValue 11RT G2 2 kVA PowerValue 11RT G2 3 kVA
Suitable for Product Class	Single-Phase UPS

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004820

External Classifications and Standards

ETIM 9	EC002850 - Accessories/spare parts for UPS
ETIM 10	EC002850 - Accessories/spare parts for UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
UNSPSC	39121601
eClass	V11.1 : 27040692
Object Classification Code	A

© 2025 ABB. All rights reserved.

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 RT G2 IEC 230V

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11RT G2 TLC 230V

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue RT G2 UL



© 2025 ABB. All rights reserved.