

**datasheet for KLEPS 2 BU**  
**article number: 973501101**

<b>product description:</b>	<b>order number: 973 501-101</b>
<b>description:</b>	Miniature clamp-type test probe with 2 mm diameter socket connection. Gold-plated copper beryllium contact spring. Gold-plated sprung bronze contact hook for wires up to a maximum diameter of 2 mm. Suitable for connection to wrap posts up to a maximum of
<b>typ:</b>	KLEPS 2 BU rot / red
<b>system:</b>	2mm system
<b>order number:</b>	973 501-101
<b>clamping range:</b>	max. Ø 2 mm
<b>clamping typ:</b>	contact hook
<b>color</b>	
<b>other color versions:</b>	
<b>technical data</b>	
<b>measurement category acc. to IEC 61010:</b>	CAT I
<b>type of termination:</b>	2 mm socket (spring-loaded)
<b>rated voltage:</b>	30 VAC / 60 VDC
<b>rated current:</b> <a href="#">Please consider derating curve!</a>	6 A
<b>contact resistance:</b>	10 mOhm
<b>material</b>	
<b>contact material:</b>	contact hook: bronze contact spring: copper - beryllium
<b>contact surface material:</b>	gold
<b>housing material:</b>	PA
<b>environmental conditions:</b>	
<b>temperature range:</b>	-25 °C to +100 °C
<b>flammable class:</b>	
<b>housing (basic material):</b>	UL 94 V - 2
<b>drawing</b>	