



R2000 – One Word only - Efficiency

Powerful Hot air gun with 3 step-position, a useful tool for versatile applications. In plastic case.

Ideal for stripping paint, taking off stickers or simply defrosting water pipes, its power of 2000 W together with its 3-step position (60, 350, 600°C on the working surface), will contribute to make of this tool your best partner for handy work. Soft grip handle and protection for secured and comfortable usage. It is not only possible to set the temperature at three levels but it is also possible to operate with different air flow rates. It's rubber base makes it stable and safe when working in desk bench position. R2000 is compatible with our range of accessories for various needs. It can be easily stored in our new sturdy plastic case.

Product Specifications

- Power : 2000 W
- Temperature : 60-350-600°C
- Airflow : 250-450 L/min
- Working voltage : 220-240V / 50Hz
- Tool weight : 0,8 kg

Features

- High airflow – 2 positions
- Double soft grip handle for high comfort
- Handle protection
- Ergonomic design
- Stable desk bench position rubber based
- 3 temperature settings
- Available in strong plastic case



Description

R2000 UK case version

Art. No

5001405

EAN

4051661033995

Measurements

330*110*290 mm

Outer

5 pcs

Weight

2,05 kg



ISABERG RAPID AB, BOX 115
SE-335 03 HESTRA, SWEDEN
www.rapid.com

Rapid®
SVENSK EFFIXITY