



Needle roller bearings NA4908-2RSR-XL (Series NA49..-2RSR)

dimension series 49, lip seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm	
D	62 mm	
B	23 mm	
C	22 mm	
F	48 mm	
r _{min}	0,6 mm	
m	252 g	Mass
C _r	41000 N	Basic dynamic load rating, radial
C _{0r}	53000 N	Basic static load rating, radial
C _{ur}	9000 N	Fatigue limit load, radial

nG Fett

5500 1/min Limiting speed for grease lubrication

