



6-2111986-3 | MP-5EMT-B-1

Modular Plug Kit, category 5e, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 100/bag

Product Classification

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Body Features

Conductor Type	Solid Stranded
Shield Material	Stainless steel
Shield Plating Material	Nickel

Configuration Features

Number of Positions	8
Keyed	No

Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm
Number of Contacts Loaded	8

Dimensions

Cable Jacket Outside Diameter Range	0.201–0.236 in 5.1–6.0 mm
Conductor Wire Size	26–23 AWG
Insulated Conductor Outside Diameter	0.035–0.043 in 0.89–1.09 mm

Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

Packaging Features

Packaging Quantity	100
--------------------	-----

Product Type Features

Cable Type	Round, shielded
------------	-----------------

6-2111986-3 | MP-5EMT-B-1

Performance Category	Category 5e
Connector Style	Plug
Jack Type	RJ45
Latch Style	Standard
Shielded	Yes

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
----------------------------------	-------------------------------------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant