

Previously known as: MICROGARD® 2000 Jacket & Trouser Set - Model 219

Superior protection from low hazard liquid spray and fine particulates with bound seams for improved overall protection..

DESIGN

MICROGARD® 2000 range is designed to allow water vapour (perspiration) to escape from the suit yet will withstand saturation of liquid chemicals and filter 100% of particulates down to 0.01 microns in size.

BOUND SEAMS

Superior strength, liquid and particle barrier

JACKET & TROUSER SET FEATURES

- Zip fastening JACKET
- Elasticated hood and hem on jacket
- Elasticated waist and ankles on trousers
- Bound seams

COLOURS

White

SIZES

S-5XL



Industries

- Life Sciences
- Metal fabrication
- Food Processing

Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Body painting including surface inspection
- Cleaning of plant and machines


KEY FEATURES & BENEFITS

- Proven protective barrier to low concentration liquid chemicals, liquid & particulate biological hazards
- Comfortable to wear featuring moisture vapor permeable fabric ("breathable") to help reduce the risk of heat stress
- Optimized fit, improving wearer comfort and safety
- Low Linting

Material Diagram



Seam Diagram



Performance Standards



PARTIAL BODY
PROTECTION ONLY



TYPE PB [6]



0598



DIN 32781



EN 14126

ASTM F1671 EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	M, L, XL, 2XL
Color	White
Country Of Origin	China
Packaging Overview	Individually Packed
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	2000 Jacket & Trouser Set - Model 219
Standards Overview	CE CATEGORY III (Type PB (6)-B, EN 14126, DIN32781)
Seam Type	Bound
Shelf Life	5 years

Suit components & accessories

Suit Components and Accessories	
Design Features	Zip fastening jacket, elasticated hood and hem on jacket, elasticated waist and ankles on trousers and bound seams.

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

