

8011TZ

Hook and jaw turnbuckle, pipe bodies DIN 1478, galvanized

CE

TECHNICAL DATA

- safety factor: 4

LABORATORY TESTS

- chemical analysis
- tensile test

AVAILABLE CERTIFICATES

- Product specification
- Test report UNI EN10204 type 2.2
- CE Declaration of Conformity



	art.	Ø mm	≈ "	L min mm	WFL kg
080110612	8011TZ	M12	1/2	260	300
080110616	8011TZ	M16	5/8	350	570
080110620	8011TZ	M20	3/4	400	900
080110624	8011TZ	M24	1"	490	1300
080110627	8011TZ	M27	1 1/8	500	2300