



.141" Tini Plug

Switchcraft® Tini-Plug® phone plugs having .141 inch diameter fingers and compatible tip shape. Mate with Switchcraft® Tini-Jax® series of miniature phone jacks.

Specifications

- Sleeve, Tip and Body: Nickel-plated copper alloy.
- Terminals: Copper alloy, electro-tinned. Solder lug or screw type (Screws #0-80).
- Handle: Molded black or red plastic. Copper alloy, nickel-plated.

Features

- Miniature 2-conductor Phone Plug for use with Switchcraft® Tini-Jax® miniature phone jacks. About 1/2 the size of Switchcraft® Littel-Plug® phone plug. Average net weight, 1/8 ounce.
- 1-piece tip rod staked into mating terminals; no disassembly of tip during use of plug. Terminals and body of plug interlocked mechanically. Can be used with cables up to .188 inch outside diameter.

Part No.	Terminals	Typical Mating Jack ¹	Handle	Part No.
740	Screw ²	41	Black	M1055
745			Red	M1056
750	Solder Lug & Cable Clamp		Black	M1055
755			Red	M1056
2P1384			Less Handle	----
770			Screw ²	Shielded
780	Solder Lug & Cable Clamp		Shielded	T13631

¹ Other mating jacks are available.

² Switchcraft® replacement Part Number P1153. 2 screws required per plug.

