

Datasheet

RS Pro M20 Red Plastic Cable Gland With Lock Nut, 7 to 10.5mm Cable Dia Range, IP55

RS Stock No: **127-316**



Product Details

RS Pro cable gland in red colour, has a thread size of M20. This cable gland with lock nut, has a cable diameter ranging from 7 to 10.5 mm. The cable made of plastic is IP55 rated. This compression type gland is supplied completely with entry thread seal.

Features and Benefits

- Made of polyamide 6
- IP55 rated
- Flammability UL 94 v2 low smoke and fume
- Complies with EU directive 2002/95/EC-ROHS
- Complies with EU directive 2002/96/EU WEEE

**Specifications:**

Cable Diameter Range	7 to 10.5 mm
Colour	Red
IP Rating	IP55
Locknut Included	Yes
Material	Plastic
Maximum Cable Diameter	10.5 mm
Maximum Operating Temperature	+80°C
Minimum Cable Diameter	7 mm
Minimum Operating Temperature	-20°C
Operating Temperature Range	-20 to +80°C
Standards Met	EN 60423, UL 94V-2
Thread Size	M20