

FEATURES

- Galvanised steel construction
- Easy to inspect for damage
- Shock absorbing
- High resistance to abrasion
- Fatigue rated at 1 – times the working load limit at 20 000 cycles

RS PRO Eye Bolt M12

RS Stock No.: 124-4842



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These Eye Bolts from our own RS PRO brand are intended for linear pulling loads in the direction of the thread. These Eye Bolts are proof tested and supplied complete with test certificate.

General Specifications

Type	Eye Bolt
Working Load Limit	0.34t
Material	Carbon Steel, C15
Finish	Zinc Plated

Mechanical Specifications

Diameter	54 mm
Thread Size	M12
Collar Diameter	30mm
Collar Thickness	11mm
Eye Outside Diameter	54mm
Weight each	0.16kg
Applications	Tensioning wires, Securing loads

Safety Standard

Standards Met	BS 4278:1984
----------------------	--------------

