

Previously known as: Nitrotough™N3500



Oil



Cut



Medium Duty

Durable cut-resistant gloves with enhanced grip, for secure, tactile handling

- **Enhanced grip:** HyFlex® 11-947 industrial working gloves boast excellent grip performance thanks to ANSELL GRIP™ coating treatment
- **Improved durability:** The three-quarter dipped coating, featuring FORTIX™ Abrasion Resistance Technology, provides ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4 protection
- **Heightened protection:** These HyFlex® gloves' INTERCEPT™ Cut Resistance Technology fiber enables these gloves to achieve ANSI/ISEA 105-2024 CUT A2 and EN ISO B levels
- **Considered aesthetics:** HyFlex® 11-947 PPE gloves' nitrile and polyurethane coating is oil- and grease-resistant, for longer wear
- **Certified harm-free:** They also possess Oeko-Tex® certification, certifying them free of harmful substances
- **Guaranteed convenience:** HyFlex® 11-947 safety gloves are also available in vend pack form, for simplified access and re-application



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Press injection molding
- Production line support & maintenance
- Inspection (picking, checking and marking)
- Changing tools and dies

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-947

Medium duty cut and abrasion resistant gloves

Previously known as: Nitrotough™N3500

Key Features

- **ANSELL GRIP™:** Industrial gloves with strong, effortless grip
- **FORTIX™ Abrasion Resistance:** Offers ANSI/ISEA 105-2024 and EN ABRASION LEVEL 4 defenses
- **INTERCEPT™ Cut Resistance fiber:** For greater laceration protection

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



DMF free



Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-947	Finishing: ¾ Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Fiber glass, Polyamide, Polyester Cuff Style: Knitwrist	13	7, 8, 9, 10	235-275 mm; 9.25-10.82 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

