

REF NO. 700024

DATE: 15/12/08

DESCRIPTION : 2 X 1.50mm² Loudspeaker Cable

CONFORMS TO: RS 626-4777

M E C H A N I C A L D A T A

- | | |
|-------------------------|--|
| 1.1. Inner Conductor: | 78 x 0.15mm Plain Stranded Copper wire
Diameter = 1.54 mm
Colours: Black, Red. |
| 1.2. Insulation: | 2.50mm |
| 1.3. Screen(s): | N/A |
| 1.4. Construction: | 2 Conductors twisted together under a PVC jacket. |
| 1.5. Jacket: | PVC (Soft Matt) |
| 1.6. Overall Diameter: | 6.60± 0.20 mm |
| 1.7. Weight: | 53 kg/km |
| 1.8. Marking: | |
| 1.9. Other details: | Max. Conductor Resistance = 13.3 Ohm/km |
| 1.10 Drawing Reference: | N/A |