

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #102153-4
020 UNIV HDR SP 4S 15DP STD




TE Part #487223-5
020 HOUSING FFC RCPT 100CL DR




TE Part #647402-3
03P SL156 HSG W/RMP&TABS,OVSZ



TE Part #796859-3
3 POS TERMI-BLOK PLUG RT ANGLE




TE Part #1393028-2
IAC-24 = PCB MONT,24V DC Logic - AC I/P



TE Part #6-1393028-4
IDC-5 = PCB MOUNT,5V DC Logic-DC I/P



TE Part #8-1734774-1
PCI EXP 2.3L 64 POS BLK 15u"



TE Part #5745078-6
HD-20 RCPT 25P VERT FFSCRLK



TE Part #6609052-2
10VN1=F7416 S0



TE Part #2-1437628-6
SPA42=SW PLATE (ON-OFF) 1/4" D

Documents

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_583671-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_583671-1_H.3d_stp.zip

English

Customer View Model

ENG_CVM_583671-1_H.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Card Guages for Dual Tine and Twin Leaf Connectors

English

Agency Approvals

UL

English