



## Rexel Momentum X308 Cross Cut Paper Shredder

The power to shred more! The Momentum X308 paper shredder shreds up to 8 sheets (80 gsm) in to P-3 (5x42mm) cross cut pieces, with a 15L bin which holds 100 A4 sheets.



## Attributes

- Shreds up to 8 sheets in one pass (80gsm)
- P-3 (5x42mm), 1 x A4 sheet into 200 cross cut pieces
- 15L bin capacity, 100 A4 sheets
- Easily shreds multiple documents, even with staples and paperclips on the corners
- 2 Year Warranty
- 2 Year Cutter Warranty



## Specifications

Number	2104570
Colour	black
Dimensions (W x H x D)	325 x 343 x 229 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	220
Run Time From Cold (min)	3
Run Time/Cool Down Time (min)	3/60
Shredded Particle Width mm	5x42
Security Level	P-3
Cutting Capacity sheets (70gsm paper)	9
Cutting Capacity sheets (80gsm paper)	8
Container/collection volume in l	15
Shreds	Paper, Paper clips & Staples
Power consumption (W)	160
Noise Level (dBA)	70
Period of Warranty (Years)	2
Location	Office
Number Of Users	1-2
Weight	3500 g
Pallet quantity	32
EAN code	5028252523202