


DEE/U 1031 Multipole Receptacles

Contact polarity A



Contact polarity Z




Panel:
Min.0
Max.12




Keying codes (View from F)



All dimensions see note 1)



Solder (-x30/-x40)




PCB (-x39/-x49)

CONTACT CONFIGURATION	Contacts	Solder cup ϕ	C	PIN ϕ
1031 A Z 010	10	0.79	-	-
1031 A Z 012	12	0.79	17.2	0.50
1031 A Z 019	19	0.43	17.2	0.40


Pin layout / PCB hole pattern for polarity A - View from F (3)

010




(4)

012





Polarity Z - View from F



(4)

019



(4)

All dimensions in mm

600541

Rev. 1

Pages 1/1

Notes:
1) All tolerances resulting from connector assembly are typically ± 0.3 mm
2) If receptacle is screwed directly into threaded hole, oversize thread by +0.05mm

3) Recommended PCB hole dimensions may be adjusted to application
4) Please contact us
Part number example : DEE 1031 A019-130



www.fischerconnectors.com