

ARCA 705030

Order symbol: ARCA 705030
Product nbr: 8120017
Description: Cabinet, PC
Remarks: 2-point locking

EAN: 6418074079282
El. number:
 Finland: 3423112
 Electric No. 8212091155
 Denmark:
 Electric No. Sweden: 2500120



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key. S versions with swinghandle 2-point locking system. F versions with flange opening (including gasket and screws). Door guide included.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	700	500	300	MPP ARCA 7050	Mounting plate perforated (630x430x2 mm - 26x11 mm)
inch:	27.6	19.7	11.8	MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - □3.6 mm)
Materials:				MPX ARCA 7050	Mounting plate (630x430 mm)
Material:	Polycarbonate			DRS ARCA 705025	DIN rail frame set
Base colour:	RAL 7035 -light grey			DRS ARCA 705030	DIN rail frame set
Cover colour:	RAL 7035 -light grey			IDS ARCA 7050	Inner door set
Gasket material:	Polyurethane			PMK ARCA 50	Pole mounting kit
Temperatures:				RCS ARCA 7050	Rain canopy set
Temperature °C (short term):	-40 ... 120 °C			SBK ARCA 50	Support bar kit
Temperature °C (continuous):	-40 ... 80 °C			SBK ARCA 70	Support bar kit
Temperature °F (short term):	-40 ... 250 °F			DSP ARCA LM	Door stopper ARCA, left, midsize, for 5070-8060
Temperature °F (continuous):	-40 ... 175 °F			DSP ARCA RM	Door stopper ARCA, right, midsize for 5070-8060

Accessories:	
MPS ARCA 7050	Mounting plate (630x430x2 mm)

Rating:
Ingress Protection (EN 60529): IP66
Impact Resistance (EN 62262): IK10 +35°C /IK08 -25°C
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Glow Wire Test (IEC 695-2-1) °C: 960

Certificates:

