

FR702 - PW3 FR Modaflame Hi-Vis Polo Shirt

Collection: PW3

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Knit HV: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre

Outer Carton: 30

Product information

Constructed using lightweight, modacrylic fabric, this polo shirt offers excellent freedom of movement due to its segmented tape design. Lightweight and stylish, this long sleeved polo shirt is the perfect choice to provide the wearer with advanced visibility and protection in hazardous situations. It features a loop at the placket ideal for attaching glasses/pens.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 4.4 CAL/CM², EBT 5.5 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

EN ISO 20471 Class 3

ASTM F1959/F1959M-12 (EBT = 4.3 CAL/CM² (HAF = 66%))



Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- High cotton content for superior comfort
- Concealed button closure
- Rib collar and cuffs
- Designed with a comfort fit
- Heat applied segmented reflective tape for added visibility
- CE-CAT III
- CE certified
- 40+ UPF rated fabric to block 98% of UV rays
- UKCA marked



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

FR702 - PW3 FR Modaflame Hi-Vis Polo Shirt

Commodity Code: 6105201000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777/13282-06/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR702YBRS	Yellow/Black	55.0	36.0	53.0	0.4650	0.1049	5036108364060	25036108853087
FR702YBRM	Yellow/Black	55.0	36.0	53.0	0.4640	0.1049	5036108364053	25036108853070
FR702YBRL	Yellow/Black	55.0	36.0	53.0	0.5050	0.1049	5036108364046	25036108853063
FR702YBRXL	Yellow/Black	55.0	36.0	53.0	0.5130	0.1049	5036108364077	25036108853094
FR702YBRXXL	Yellow/Black	55.0	36.0	53.0	0.5390	0.1049	5036108364084	25036108853100
FR702YBRXXXL	Yellow/Black	55.0	36.0	53.0	0.5590	0.1049	5036108364091	25036108853117