

317466

Broom, 410 mm, Soft/hard,  
Brown



Designed for effective cleaning of food industry floors as well as in kitchens and restaurants, this Broom has firm front bristles that loosen stubborn dirt and heavier debris, while the softer rear bristles gather the finer particles.

# Technical Data

<b>Item Number</b>	317466
<b>Visible bristle length</b>	52 mm
<b>Material</b>	Polypropylene Polyester Stainless Steel (AISI 304)
<b>Complies with (EC) 1935/2004 on food contact materials<sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	480 Pcs.
<b>Quantity Per Layer (Pallet)</b>	60 Pcs.
<b>Box Length</b>	545 mm
<b>Box Width</b>	270 mm
<b>Box Height</b>	220 mm
<b>Length/Depth</b>	410 mm
<b>Width</b>	90 mm
<b>Height</b>	120 mm
<b>Gross Weight</b>	0,54 kg
<b>Net Weight</b>	0,51 kg
<b>Cubik metre</b>	0,0044 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. cleaning temperature (Dishwasher)</b>	93 °C
<b>Max. usage temperature (for food contact)</b>	80 °C
<b>Max usage temperature (non food contact)</b>	100 °C
<b>Min. usage temperature<sup>3</sup></b>	-20 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705022013872
<b>GTIN-14 Number (Box quantity)</b>	15705028013903
<b>Commodity Code</b>	96039099
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care

units, before use.

3. Do not store the product below 0° Celsius.