



Cut



Medium Duty

Highly cut-resistant ambidextrous industrial gloves, ideal for food handling applications

- **Advanced defenses:** HyFlex® 74-500 safety gloves' liner blends fiber glass, stainless steel, HPPE, polyamide, and polyester with INTERCEPT™ Cut Resistance Technology, for advanced 360° protection
- **Improved durability:** These abrasion-resistant gloves remain durable and maintain performance levels even with repeated laundering, while also masking stains thanks to their blue color, extending overall wear life
- **Food handling compliance:** Compliant with FDA food handling regulations 21 CFR 177.1520 and 21 CFR 177.2600, these HyFlex® gloves are suited to various food processing applications
- **Genuine practicality:** Comfortable by nature, they also boast an ambidextrous design, for greater everyday ease of use



Industries

- Food Processing

Applications

- Dairy Processing
- Fruit and Vegetable Processing
- Poultry Processing

HyFlex[®]

ADVANCED MECHANICAL PROTECTION

74-500

Highest cut level food certified glove

Key Features

- **Fiber glass- and stainless steel-infused liner:** Superb cut resistance
- **Durable materials:** Heightened abrasion resistance, longer wear life*
- **FDA food handling compliance:** Suitable for varied food processing
*7x more durable than close competitors

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



4X4XF

EN 388



4X4XF



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	PACKAGE
HyFlex [®] 74-500	Liner Material: HPPE, Fiber glass, Stainless steel, Polyamide, Polyester, Ansell INTERCEPT™ Technology Cuff Style: Knitwrist	10	7, 8, 9, 10	225-270 mm; 8.8-10.6 inches	6 pairs/bag, 2 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, [®] and [™] are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell