

HONEYWELL PART NUMBER
411SX21-T
PRODUCT CODE VDX1121
MILITARY PART NUMBER M8805/106-01

REV	DOCUMENT	CHANGED BY	CHECK
3	0038558	SS 08MAY08	BLR

B


A

A


B

A

A




PLASTIC PLUNGER



NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
- 2 TERMINALS ARE PLATED FOR SOLDERING
- 3 SWITCH WILL WITHSTAND TEMPERATURE OF 400°F

RELEASE NO. PR-10353
REPLACES

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH		DRAWN	SPK	29FEB08	Honeywell				
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT SPDT			TOLERANCES UNLESS NOTED:		CHECK	RJ	29FEB08					
RELEASE FORCE ----- 1 OZ MIN					NO PLACE X ±		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL -- .002 MAX					ONE PLACE .X ±									
OVERTRAVEL ----- .004 MIN					TWO PLACE .XX ±									
					THREE PLACE .XXX ±									
					FOUR PLACE .XXXX ±									
					ANGLES ±		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
					THIRD ANGLE PROJECTION		RASTER			B	I	411SX21-T		3
										SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1	
		APPROVALS												
		MILITARY	M8805/106-01		BRAND									