




All Nylong Vertical PCB Header: 2.54mm, Through Hole, MTA 100 (25)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought



TE Part #1-2834015-6
6POS 2.54MM TES CONN.



TE Part #1-640455-6
16P MTA100 HDR ASSY SQ R/A POL




TE Part #292206-5
MINI CT SGL DIP H 5P NAT



TE Part #3-640431-6
06P MTA156 CONN ASSY 18AWG ORA



TE Part #644753-6
06P MTA156 HDR ASSY RN STR F/L



TE Part #CAT-104MTA-NGPNR
Nylon Gold Plated Receptacle: 2.54 mm, no Mating Alignment



TE Part #1-640453-6
16P MTA100 HDR ASSY SQ R/A



TE Part #6609113-9
6CFE1=F7833 S0

Documents

- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-647047-5_F_c-3-647047-5-f.2d_dxf.zip

English
- Customer View Model

ENG_CVM_CVM_3-647047-5_F_c-3-647047-5-f.3d_igs.zip

English
- Customer View Model

ENG_CVM_CVM_3-647047-5_F_c-3-647047-5-f.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English