



ENGLISH

European 2-Pin Plug-in top Power Supply 15vdc 7.5watt



The RS Pro Range of Class II 7.5watt AC/DC European plug-in power supplies provide 7.5 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Features:

- European Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved





ENGLISH

Specification	
RS Stock Number	1753300
Input Voltage Range	100-240Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.4A Max
Output Voltage Rating	+15V
Output Current Range	0.5A
Output Min Current	0.01A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	150mVp-p
Efficiency	80.44%Min
Over Voltage Protection	16vdc Max
Over Load Protection	1.4A
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet TUV (EN60950-1)
EMI Standard	Meet CE (Declared& CE Mark)
MTBF	50,000 hours
Size mm max.	78.98(L) 41 (W) * 49.2(H)
Weight	110 g
Regulator Type	Switched Mode Power Supply