



Part Number : [732760161](#)

Product Description : N Jack, Straight, Bulkhead, Crimp, LMR-400 Cable, Brass Body, Nickel (Ni) Plated, 50 Ohms

Series Number : 73276

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[732760161_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	N Jack, Straight, Bulkhead, Crimp, LMR-400 Cable, Brass Body, Nickel (Ni) Plated, 50 Ohms
Product Name	N
Style	Cable
Type	Medium
UPC	822350926782

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Jack
Keying to Mating Part	N/A
Net Weight	44.313/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	LMR-400

This document was generated on Aug 11, 2025