

TECHNICAL DATA SHEET

SRC02B HYGIENE CLOG

**WASHABLE
MICROFIBRE
UPPER**

**PROTECTIVE STEEL
TOE CAP**

**SELF-CLEANING
ANTI-SLIP SOLE**



DESCRIPTION

Ideal for indoor cleanroom environments such as food preparation, medical and pharmaceutical where there is a risk of slipping on wet or dry tiled surfaces, Blackrock's Hygiene Clog features a steel toe cap and water resistant microfibre upper that can be machine washed at 40°C. The lightweight, anti-slip PU sole is self-cleaning, anti-static and resistant to oils, acids and fuel oil.

SIZES

Size 3-13 (available
in size 6.5 and 10.5)

STANDARDS

EN20345 S2 SRC

KEY FEATURES

- Machine washable at 40°C
- Steel toe cap with anti-slip, self-cleaning sole
- Energy absorbing heel reduces foot fatigue

FEATURE ICONS



TECHNICAL DATA SHEET

MATERIALS

- Microfibre upper
- PU sole
- Steel toe cap

TYPICAL INDUSTRIES

- Pharmaceutical
- Hygiene & catering

CERTIFICATION/MARKINGS



EN ISO 20345:2011 is an internationally recognised standard which specifies requirements for safety footwear. Any product which references an EN standard must have the relevant certification attributed to the product code found on the product.

The product standard can be found on the tongue label and should match that stated on the certification. The standard is usually a group of numbers and letters, for example S3 WR HRO SRC. These letters and numbers denote the characteristics that make up the footwear you are buying which include properties such as protective toe cap, water-resistant uppers, protective midsole, fuel oil resistance, anti-static, heat resistance and slip resistance.

Users are advised to select the required class of performance based on the risk assessment of the location and/or task as appropriate.

PRODUCT DETAILS

CODE	SIZE	COLOUR	BARCODES	PACKAGING
SRC02B03	3	Black	5019200195770	Each pair individually boxed Purchase multiple: 1 Outer carton quantity: 10 
SRC02B04	4	Black	5019200195787	
SRC02B05	5	Black	5019200195794	
SRC02B06	6	Black	5019200195800	
SRC02B065	6.5	Black	5019200196012	
SRC02B07	7	Black	5019200195817	
SRC02B08	8	Black	5019200195824	
SRC02B09	9	Black	5019200195831	
SRC02B10	10	Black	5019200195848	
SRC02B105	10.5	Black	5019200196029	
SRC02B11	11	Black	5019200195855	
SRC02B12	12	Black	5019200195862	
SRC02B13	13	Black	5019200195879	