

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)
	CURRENT	0.5 A (note 1)	APPLICABLE CABLE	t=0.3±0.03mm, GOLD PLATING

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
------	-------------	--------------	----	----

CONSTRUCTION

GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.		x	x

ELECTRICAL CHARACTERISTICS

VOLTAGE PROOF	150 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	x	x
INSULATION RESISTANCE	100 V DC.	500 MΩ MIN.	x	x
CONTACT RESISTANCE	AC 20 mV MAX (1 KHz), 1 mA .	100 mΩ MAX. INCLUDING FPC,FFC BULK RESISTANCE (L=8mm)	x	x

MECHANICAL CHARACTERISTICS

VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, m/s^2 FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 100 mΩ MAX.	x	—
SHOCK	981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.	③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
FPC RETENTION FORCE	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)	① DIRECTION OF INSERTION : 0.15N × n MIN. ② VERTICAL DIRECTION OF INSERTION : 0.15N × n MIN. (note 2)	x	—
LOCK OPERATION FORCE	MEASURED BY APPLICABLE FPC. (THICKNESS OF FPC SHALL BE t=0.30mm AT INITIAL CONDITION.)	① CLOSING FORCE : 0.1N × n MAX.(12 ~ 32 POS.) ② OPENING FORCE : 0.05N × n MIN.	x	—

ENVIRONMENTAL CHARACTERISTICS

CORROSION SALT MIST	EXPOSED AT 35 °C , 5 % SALT WATER SPRAY FOR 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS. ③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	x	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 → +15 TO +35 → +85 → +15 TO +35 °C TIME 30 → 2 TO 3 → 30 → 2 TO 3 min UNDER 5 CYCLES.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.		x	—
DAMP HEAT, CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES, TOTAL 240 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—

COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				

REMARK	APPROVED	HS. SAKAMOTO	16.09.29
	CHECKED	YH. MICHIDA	16.09.28
	DESIGNED	SI. MIZUSAWA	16.09.28
	DRAWN	KY. KIKUCHI	16.09.27

Unless otherwise specified, refer to IEC 60512.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC-155115-99-00
--	-------------	------------------

HRS	SPECIFICATION SHEET	PART NO.	FH19SC-**S-0.5SH(99)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL580	△ 1/2

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
DRY HEAT	EXPOSED AT 85 °C, 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX.	x	—	
COLD	EXPOSED AT -55°C, 96 h.	② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—	
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40 °C , RELATIVE HUMIDITY 80% , 25±5 ppm FOR 96 h.	① CONTACT RESISTANCE: 100 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—	
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40 °C , RELATIVE HUMIDITY 80% , 10 TO 15 ppm FOR 96 h.	③ NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	x	—	
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 235±5°C FOR IMMERSION DURATION, 2±0.5 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	x	—	
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING : PEAK TMP. 250 °C MAX . REFLOW TMP. OVER 230 °C WITHIN 60 sec. 2) SOLDERING IRONS : TMP. 350 ± 5 °C FOR 5 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	x	—	
<p>(note 1)</p> <p>WHEN THE SAME VALUE OF CURRENT ARE APPLIED TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.</p> <p>(note 2)</p> <p>THIS PRODUCT HAS FLIP-LOCK CONSTRUCTION. FASTEN FPC ON PCB OR SOMETHING FIXED IF FORCE IN VERTICAL DIRECTION SHALL BE PREDICTED.</p>					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-155115-99-00
HRS	SPECIFICATION SHEET		PART NO.	FH19SC-**S-0.5SH(99)	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL580	△ 2/2