



ENGLISH

Spanner Sets

12 PC Flexible Ratchet Gear Spanner Set



[RS Stock Number 487-268](#)

**Material**

Drop forged chrome vanadium steel (cr-v#6140) for spanners body
Chrome molybdenum steel (Scm-440) for ratchet gear and pawl

Finish

Chrome plated with mirror polish spanner body, Phosphate finish for ratcheting gear

Hardness

Heat treated to HRC 42~48 for spanner body
HRC 48~52 for ratcheting gear and pawl

Contents

12pcs- 72 teeth one-way flexible head, ratcheting combination spanners (5 degrees for each ratcheting) with black colour injection rack

Sizes

8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19mm

Remark

Hardness of spanner body meets din 899-row
Torque tests of box end meet din 899-row
Open end meet Din 899-row c and go, no-go gauges of both box and open end meet din 475 part row 1 requirements.

Features

Patented surface drive reduce fastener rounding
Flex head tilts up to 180 degree at any interval
Set screw allows you to set head tension
Ratcheting box-end needs as little as 5 degree turn to move fastener
Designed for a tight space , sleek head design enables access to tight spots where a ratchet will not fit