



ENGLISH

Datasheet

## RS Pro PMP Laboratory Cylinder, 250mL

RS Stock No: **892-0003**



### Product Details

RS Pro PMP laboratory cylinder with class A calibration, has a capacity of 250 ml, it features enhanced pin-sharp blue-printed graduations and stable hexagonal bases which have a non-slip anti-suction feature.

### Features and Benefits

- PMP confers hardness, solidity, low density, transparency and chemical resistance
- Steam sterilisation at 121°C does not affect accuracy
- Calibrated to ISO 6706 and DIN 12681, class A tolerances



**Specifications:**

Capacity	250 ml
Graduations	Yes
Length	315 mm
Material	PMP
Base Shape	Hexagonal
Cylinder Class	Class A
Graduation Increments	2 ml
Tolerance	±1