



#### General ordering data

Order No.	8794120000
Part designation	JP TEST
Version	Test adapter, 18...24...30 V DC , 2 A, M12 plug/ socket, A-coded
EAN	4032248483969
Qty.	1 pc(s).

#### Input

Rated control voltage	18...24...30 V DC
Rated current DC	2.2mA (LED)
Status indicator	Green LED

#### Output

Continuous current	2 A
--------------------	-----

#### Rated data

Connection system	M12 plug/socket, A-coded
Storage temperature	-25 °C...+70 °C

#### Dimensions

Length	83 mm
Height	14.4 mm
Width	36 mm

#### Approvals

Approvals institutes	ř.ä.
----------------------	------

#### Classifications

eClass 4.1	NK
eClass 5.0	NK
eClass 5.1	NK