




Datasheet


HSS 43 mm 90° Countersink, 20.5mm Head Diameter, 3 Flutes

RS Stock number 423-822



Dimensions:





NOMINAL HEAD DIA.	OVERALL LENGTH (D)	SHANK LENGTH(I)	HEX SHANK DIA.(d)	POINT ANGLE	NO. OF FLUTE
6.3mm	31mm	21.5mm	7.15mm	90°	3
8.3mm	32mm	21.5mm	7.15mm	90°	3
10.4mm	34mm	21.5mm	7.15mm	90°	3
12.4mm	36mm	21.5mm	7.15mm	90°	3
16.5mm	40mm	21.5mm	7.15mm	90°	3
20.5mm	43mm	21.5mm	7.15mm	90°	3

Remarks:

- Material: HSS M2

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.