



Multi Purpose Abrasion Protection



Light Duty

Ultralight multi-purpose gloves, designed for comfortable, tactile handling

- **Heightened tactility and dexterity:** HyFlex® 11-818 safety gloves' lightweight 18-gauge liner and thin coating grant them a "second skin" feel
- **Improved durability:** Their FORTIX™ Abrasion Resistance nitrile coating helps them achieve ANSI/ISEA and EN compliant abrasion resistance
- **Enhanced grip:** The same nitrile foam coating ensures excellent grip, especially in dry conditions
- **Elevated comfort:** HyFlex® 11-818 industrial gloves' ZONZ™ Comfort Fit knitwork relieves tension in stress-prone areas
- **Enhanced breathability:** As their coating is thin and palm-dipped, hand protection is more breathable
- **Certified skin-friendliness and cleanliness:** Dermatest® certification ensures skin-friendliness, while impurities are extracted through a proprietary washing process



Industries

- Automotive
- Machinery and Equipment
- Chemical
- Utilities
- Warehousing
- Food processing and handling

Applications

- Adjusting parts, systems
- Mounting and dismantling
- Final assembly
- Loading and unloading trucks and vehicles
- Handling incoming goods
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Loading trucks & vehicles
- Product shipping, transport and delivery
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Lock smith
- Dry food handling & packaging
- Compatible with consumer and industrial touchscreens

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-818

Our lightest Multi-Purpose glove for ultimate dexterity

Key Features

- **Light 18-gauge liner:** For PPE gloves with "second skin" tactility
- **Thin nitrile foam coating:** Added grip and highly breathable
- **ZONZ™ Comfort Fit:** Optimized knitwork for reduced tension and strain

Technologies



DMF free



FORTIX™

Abrasion Resistance Technology



Touchscreen Compatible



ZONZ™

Comfort Fit Technology

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



EN388: 2016



3121A



STANDARD 100

1408033
Centexbel

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-818	Finishing: Palm Coated Coating Material: Foam Nitrile Liner Material: Nylon, Spandex Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11, 12	200-270 mm/ 7.9-10.6 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell