




**Part Number :** [2077820212](#)  
**Product Description :** Squba 3.6 Sealed  
Receptacle Assembly, 3.60mm Pitch, 2  
Circuits, Single Row, Glow-Wire Capable, Key  
B, Natural, UL1015/UL1230 Compatible  
**Series Number :** 207782  
**Status :** Active  
**Product Category :** Connector Housings



## Documents & Resources

### Drawings

[2077820212\\_sd.pdf](#)  
[2077820000-PK-000.pdf](#)

### 3D Models and Design Files

[2077820212\\_stp.zip](#)

### Specifications

[2077760000-AS-000.pdf](#)  
[2077760000-PS-000.pdf](#)  
[2077760000-TS-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                |
|--------------------|------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                   |
| China RoHS         |                                                |
| EU ELV             | Not Relevant                                   |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21             |
| REACH SVHC         | Not Contained per D(2024)6225-DC (07 Nov 2024) |
| EU RoHS            | Compliant per EU 2015/863                      |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

## Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

|              |                                                                                                                                         |
|--------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Status       | Active                                                                                                                                  |
| Category     | Connector Housings                                                                                                                      |
| Series       | 207782                                                                                                                                  |
| Description  | Squba 3.6 Sealed Receptacle Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, Key B, Natural, UL1015/UL1230 Compatible |
| Application  | Power, Signal, Wire-to-Wire                                                                                                             |
| Product Name | Squba                                                                                                                                   |
| UPC          | 196823171949                                                                                                                            |

#### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

#### Physical

|                       |            |
|-----------------------|------------|
| Circuits (maximum)    | 2          |
| Color - Resin         | Natural    |
| Flammability          | 94V-0      |
| Gender                | Receptacle |
| Glow-Wire Capable     | Yes        |
| Keying to Mating Part | None       |
| Lock to Mating Part   | Yes        |
| Material - Resin      | Nylon      |
| Net Weight            | 3.278/g    |
| Number of Rows        | 1          |
| Packaging Type        | Tray       |

|                               |                |
|-------------------------------|----------------|
| Panel Mount                   | No             |
| Pitch - Mating Interface      | 3.60mm         |
| Pitch - Termination Interface | 3.60mm         |
| Polarized to Mating Part      | Yes            |
| Temperature Range - Operating | -40° to +105°C |

---

## Mates With / Use With

### Mates with Part(s)

| Description                                                                                                                                      | Part Number       |
|--------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|
| Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, Key B, Natural, UL1015/UL1230 Compatible                | <u>2077780212</u> |
| Squba 3.6 Sealed Plug Assembly, 3.60mm Pitch, 2 Circuits, Single Row, Glow-Wire Capable, with Clipslot, Key B, Natural, UL1015/UL1230 Compatible | <u>2077781212</u> |

### Use with Part(s)

| Description                                                                                 | Part Number       |
|---------------------------------------------------------------------------------------------|-------------------|
| Squba 3.6 Receptacle Terminal, Matte Tin Plating, UL1015/UL1230 Compatible, 20-18 AWG, Reel | <u>2077770003</u> |