



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #6-1879497-5
CRGH1206 5% 470R 0.5W

TE Part #1SNK706412R0000
ZK2.5-SF-R3

TE Part #1-2176411-0
1/2W SM M/OX 5% 27K

TE Part #1676472-2
RN 0805 9K09 0.1% 10PPM 1KRL

TE Part #4-1676915-5
YR1 0.1% 9K09

TE Part #1SNK705030R0000
ZK2.5-OR

TE Part #CAT-55M-SCH-HW
Hookup wire: Silver Coated Wire, 450V
Dual Wall

TE Part #8-1614352-2
RN 0805 392K 0.1% 10PPM 1K RL

TE Part #1SNK705060R0000
ZK2.5-YL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1887202-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1887202-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1887202-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Interface Plug-in Relay XT

English

Accessories - Power Relay XT

English



Product Specifications

Definitions General Purpose Relays

English