

/ RUN-R 500 / 62673 / EN 20345:2011 S1P SRC

**100%
metal
free**

Sporty safety shoe

- Lightweight
- Flexible
- Comfortable
- Breathable upper
- Antistatic
- 100% metal free
- Sizes : 35 - 48



APPLICATIONS //

Light industry, warehousing and logistics, maintenance, assembling, tradesmen, manufacturing, dry environments

TECHNICAL SPECIFICATIONS //

- **PU2D sole:** very lightweight, highly flexible, excellent shock absorption, grip SRC | oil, hydrocarbon and chemical resistant, antistatic | grooves at the back of the heel for a better grip when the heel first touches the ground and deep grooves for better grip in the forefoot area | pronounced heel and GRIPSTEP profile for ladders and stairs
- **Upper:** breathable mesh with TPU film in forefoot, heel and lacing areas for a better abrasion resistance
- **Quarter lining:** polyester mesh 3D, excellent breathability, quick drying
- **Vamp lining:** non-woven for excellent abrasion resistance
- **Tongue:** breathable textile with stretch gussets for support and comfort without any intrusion of dirt or debris | loop to adjust at best the position of the tongue
- **Collar :** soft and compact foam for better comfort and protection
- **Composite toe cap:** antimagnetic, lighter than a conventional steel toe cap, conducts less heat and cold than a metal toe cap
- **Composite penetration resistant midsole:** flexible | antimagnetic | protects 100 % of the surface of the foot (as opposed to 85 % on average for steel soles) | lighter than steel soles | conducts less heat and cold than a metal sole
- **Hygienic insole:** removable, anatomically shaped with front and heel shock absorption | high quality microfibre top layer, excellent abrasion resistance, moisture absorption, quick drying, shock absorption, arch support | bottom layer open cell foam: good moisture absorption and wicking properties, quick drying | washable at 30°C
- French (EU) sizing system, width 11
- **Weight:** 510 g per foot, in size 42