

Features

- Versatile single layer foam anti-fatigue mat.
- Insulates standing workers against the effects of cold concrete floors.
- Lightweight, so easy to transport and reposition.
- Best suited to dry environments.
- High visibility version available with bright yellow borders.
- Stylish ribbed surface pattern.
- Available in mats and rolls.
- Ideal for lighter industrial use where the user doesn't turn regularly in a static position.
- Fire tested to BS EN 13501-1.

RS PRO Ribbed Anti-Fatigue Mat for Dry Workplaces

RS Stock No.: 0726297



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- Versatile single layer foam anti-fatigue mat.
- Insulates standing workers against the effects of cold concrete floors.
- Lightweight, so easy to transport and reposition.
- Best suited to dry environments.
- High visibility version available with bright yellow borders.
- Stylish ribbed surface pattern.
- Available in mats and rolls.
- Ideal for lighter industrial use where the user doesn't turn regularly in a static position.
- Fire tested to BS EN 13501-1.

General Specifications

Size	0.9 m x 1.5 m
Product Height	9.5 mm
Colour	Grey/Yellow
Weight (kg)	3
Size of Safety Border	100 mm
Material	Open Cell PVC (Foam)
Surface Finish	Ribbed
Min. Operating Temperature	0°C
Max. Operating Temperature	+60°C
Environmental Resistance	Suitable for dry indoor environments
Typical Applications	Production lines, Assembly areas, Packing stations, Workbenches
Installation Method	Loose lay
Cleaning Method	Brush/mop the top surface

Similar Products

Stock No.	Brand	Product Name	Size	Colour	Weight (kg)
0726294	RS PRO	Orthomat Ribbed	0.6 m x 0.9 m	Black	1.5
0726295	RS PRO	Orthomat Ribbed	0.9 m x 1.5 m	Black	3
0726296	RS PRO	Orthomat Ribbed	0.6 m x 0.9 m	Grey/Yellow	1.5