

PRODUCT-DETAILS

TY253M-3

CABLE TIE 50LB 11IN ORANGE NYLON



General Information

Extended Product Type	TY253M-3
Product ID	7TAG009270R0004
EAN	5414363062349
Catalog Description	CABLE TIE 50LB 11IN ORANGE NYLON
Long Description	High Performance Cable Tie for Indoor applications, Orange Color Nylon 6.6, Length of 295mm (11.6 Inches) for Bundle Diameter up to 78mm (3.07 Inches), Width of 4.9mm (0.19 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -60 Degrees Celsius (-76 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/215 Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Military Specified (MIL-SPEC MS3367-7-3), Bulk Pack

Ordering

EAN	5414363062349
UPC	786210903255

Dimensions

Product Net Width	0.189 in 4.82 mm
Product Net Depth / Length	11.4 in 289.7 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	13 in 330 mm
Package Level 2 Height	12.5 in 318 mm
Package Level 2 Depth / Length	14 in 356 mm

Technical UL/CSA

Flammability According to UL94	V-2
-----------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Orange
Effective Date	19921027
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000518
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY253M-3

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

