



PRODUCT-DETAILS

CEM11-FBP.120

CEM11-FBP.120 Earth Leakage Monitor 120 mm $\square$, setting 0.24 ...13.6 A



概要信息	
产品型号	CEM11-FBP.120
产品ID	1SAJ929200R0120
欧洲商品编号(EAN)	4013614398421
目录说明	CEM11-FBP.120 Earth Leakage Monitor 120 mm $\square$, setting 0.24 ...13.6 A
详细描述	CEM11-FBP.120 Earth Leakage Monitor features a 120 mm diameter through-hole. A threshold can be set, upon violation of this threshold a binary signal is outputted.

订货信息	
最小起订量	1 piece
海关关税号	85043129
产品系列	CEM11-FBP

Popular Downloads	
数据手册, 技术资料	2CDC135010D0204
说明书和手册	2CDC135010D0204

尺寸

产品净宽	210 mm
产品净深	190 mm
产品净高	38 mm
产品净重	940 g

技术参数

连接容量	1x 0.75-1.5 mm ²
安装位置	Any
安装类型	Screw
安装到DIN导轨上	No
功率损耗	Approximately 0.2 W
额定控制供电电压 (U _s)	24 V DC
额定频率 (f)	Main Circuit 50 / 60 Hz
推荐的螺丝刀	Pozidriv 1
设置范围	0.3 ... 13.6 A
标准	IEC/EN 60947-1 IEC/EN 60947-4-1
适用于	UMC100-FBP UMC100.3
适用产品系列	Universal Motor Controllers
拧紧力矩	Auxiliary Circuit 0.6 ... 1 N·m Control Circuit 0.6 ... 1 N·m
剥线长度	7 mm

UL/CSA适用的技术参数

连接容量UL/CSA	Flexible with Ferrule 1x 18-16 AWG Rigid 1x 18-16 AWG
------------	--

环境条件

防护等级	IP20
------	------

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SAA983001-4501
RoHS信息	1SVD981041-00
RoHS状态	Following EU Directive 2011/65/EU
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

ATEX认证	Not available
符合性声明 - CE	1SVD981041-00

包装信息

1级包装单元	box 1 piece
1级包装宽度	210 mm
1级包装长度	190 mm
1级包装高度	38 mm
1级包装 总重	0.945 kg
1级包装 EAN	4013614398421

分类

e级	V11.0 : 27242608
E-Number (Finland)	3709077
E-Number (Norway)	4552500
ETIM 6	EC001604 - Fieldbus, decentr. periphery - communication module
ETIM 7	EC001604 - Fieldbus, decentr. periphery - communication module
ETIM 8	EC001604 - Fieldbus, decentr. periphery - communication module
ETIM 9	EC001604 - Fieldbus, decentr. periphery - communication module
IDEA 粒度分类代码 (IGCC)	6312 >> Earth leakage devices
对象分类代码	B
UNSPSC	41113645

分类

低压产品及系统 → 控制产品 → 电动机控制器 → 智能电机控制器附件

