



## PW3 HI-VIS COTTON COMFORT POLO SHIRT S/S

### DESCRIPTION

Constructed from premium breathable Cotton Comfort fabric combined with HiVisTex Pro tape, this polo shirt offers excellent comfort and movement. It features a loop at the placket ideal for attaching glasses/pens.

### COMPOSITION

55% Cotton, 45% Polyester, Knit, 175g  
 Orange/Black XS-5XL

### FEATURES

- Moisture wicking fabric helping to keep the body cool and dry
- High cotton content for superior comfort
- Loop at placket ideal for attaching glasses/pens
- Side vents for added comfort
- Designed with a comfort fit
- Heat applied segmented reflective tape for added visibility
- Chest pocket
- 40+ UPF rated fabric to block 98% of UV rays
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified
- UKCA marked

### STANDARDS

EN ISO 20471 Class 2  
RIS 3279 TOM Issue 2 (Orange Only)  
ANSI/ISEA 107 Type R Class 2  
ANSI/ISEA 107 TYPE P CLASS 2

### COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T180OBR	ORANGE/BLACK	XS-5XL

### FEATURES





**STANDARDS**



**EN ISO 20471**  
High Visibility Clothing - Test Methods  
And Requirements




**PERFORMANCE WORKWEAR**

PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

**GET THE COLLECTION**



**TECHINCAL INFORMATION**



**SATRA Technology Europe Ltd**  
(Notified Body Number.: NB: 2777) Bracetown  
Business Park Clonee Dublin 15 D15 YN2P, Ireland  
Cert No: 2777/11506-03/E00-00

**OEKO-TEX certification**  
11-34354

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m <sup>3</sup> )	EAN13	GTIN/DUN14
T180BRXS	Orange/Black	55	36	34	.298	1402.500	5036108306893	15036108795977
T180OBRS	Orange/Black	55	36	34	.286	1402.500	5036108287765	15036108777904
T180OBRM	Orange/Black	55	36	34	.296	1402.500	5036108287758	15036108777898
T180OBRL	Orange/Black	55	36	34	.325	1402.500	5036108287741	15036108777881
T180OBRL	Orange/Black	55	36	40	.350	1650.000	5036108287772	15036108777911
T180OBRL	Orange/Black	55	36	40	.360	1650.000	5036108287789	15036108777928
T180OBRL	Orange/Black	55	36	40	.378	1650.000	5036108287796	15036108777935
T180OBRL	Orange/Black	55	36	40	.390	1650.000	5036108309634	15036108798237
T180OBRL	Orange/Black	55	36	40	.398	1650.000	5036108346837	15036108835406