



Brand of NTN Group

Technical data

UC308G2

Insert bearings



Spherical outer diameter, fixing by socket set screw, seal with slinger

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
B - Width of Inner Ring	52 mm
C - Width of Outer Ring	28 mm
C1 - Distance center of OR to center of lubrication zone	8,5 mm
d - Shaft diameter	40 mm
D - Outer diameter of OR	90 mm
G - Set screw size	M10x1,25
m - Distance to set screw	10 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

r - Radius Inner Ring	2
S - Distance front side/bearing centre	19 mm
f0 - Factor	13.2
SW - Wrench size	5 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	40560000 mN
C0 - Static load rating	24000000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	0,96 kg
Recommended tightening torque for set screw	22 N-m

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	3.0790106870229 Hz
BPMF - Over rolling frequency on inner (60 rpm)	4.9209893129771 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	4.11290838880742 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.05645419440371 Hz
FTF - Rotational frequency - cage (60 rpm)	0.384876335877863 Hz

