

TruCheck 2 Plus, 50 - 1,100 N·m



TruCheck™ 2 is a cost effective torque wrench checker that has been redesigned to incorporate improved features whilst maintaining ease of use.

The TruCheck™ 2 aims to cut the cost of purchasing a torque wrench checking system and remove the reservations over the complexity of using such equipment.

Part number: 43531

EAN Bar Code: 5060207566537

NATO number: -

Accuracy: -

Operates between:

50.00 - 1100.00 N·m



TECHNICAL SPECIFICATIONS

- Weight: 3.5 Kg
- Accuracy: $\pm 1\%$ torque reading accuracy ($\pm 2\%$ when below 10% of range for the 1,100 N·m TruCheck™ 2 model)
- Display: LCD Display
- Temp Range - Operating: 0°C to $+50^{\circ}\text{C}$
- Temp Range - Storage: -20°C to $+70^{\circ}\text{C}$
- Auto Reset Hold Time: 1,2 or 3 seconds
- Power Consumption: 0.5W
- Electromagnetic Compatibility (EMC) Directive: Designed to comply with EN 61326-1
- Requires two Hexagon Socket Head Cap Screws ISO 4762 - M10 - 12.9 to fix in position (not included)
- Environment: IP 40

FEATURES

- Allows torque wrench performance to be monitored and tools to be kept in peak condition
- Allows a selection of torque units, three modes of operation (Click, Dial and Track), the ability to store up to 15 targets and select from 12 languages
- Allows operator to set a target value and tolerance
- Inbuilt Micro USB 2.0 port enables power from any USB power source. Plus versions allows for both power and data transfer simultaneously
- Supplied with 27 mm male hexagon plus 3/4" female square drive adapter
- If you order a UKAS accredited calibration certificate (available at extra cost) this certificate will be provided in place of the traceable calibration certificate
- Software can be updated remotely, without the need to return the product to Norbar
- Supplied with traceable calibration certificate in clockwise direction. A counter-clockwise calibration is available at additional cost

DIMENSIONS & WEIGHT

Tool Weight: 7.50


Packed Weight: 8.50

Dimensions: 100 x 100 x 100 mm

Packed Length: 620.00

Packed Height: 520.00

Packed Width: 270.00



NORBAR TORQUE TOOLS LTD. Wildmere Road, Banbury, Oxfordshire,
OX16 3JU, United Kingdom
Registered Office as above - Registered in England No. 380480 - VAT No.
GB 119 1060 05

- Tel: + 44 (0) 1295 270333
- Enquiries: + 44 (0) 1295 753600
- After Sales : + 44 (0) 1295 753635
- Fax: + 44 (0) 1295 753609
- Email: enquiry@norbar.com
- Repairs: repairs@norbar.com