

DATA SHEET: FLS##PBK SERIES



IP44 LED Floodlight with PIR



MLA part code:	FLS15PBK	FLS30PBK	FLS50PBK
Description:	15W PIR LED	30W PIR LED	50W PIR LED
Finishes:	Black		
Weight (kg):	0.81	1.48	2.54
Wattage (W):	15	30	50
Overall dimensions (mm):	115(l) 181(h) 88(p)	181(l) 216(h) 112(p)	223(l) 256(h) 135(p)
ErP Class:	A	A+	A+
Lumen Output (lm):	1200	2700	4800
CCT:	6000K		
LED Colours:	Day Light		
Input voltage:	Mains 230V 50Hz		
Construction:	Die cast Aluminium		
Driver required:	No		
Class:	Class I		
IP rating:	IP44		
Life span:	25,000 hrs		
Pre Wired:	Yes with 300mm cable		
Warranty:	3 Year		
Dimmable:	No		
Instruction sheet:	Yes		
Origin of Manufacture:	China		
Quality assurance system:	ISO9001		
Declaration of Conformity (held on file):	Yes		
Manufactured in accordance with:	EN60598-2-5		

