

Features

- Electrical control with touch button
- 3 speeds
- Natural breeze + Sleep mode
- Automatic oscillation, up to 72°
- Remote control

RS PRO Tower Fan 12.14m³/min, 3 speed 230 V with Type G – British 3-pin

RS Stock No.: 0227903



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Tower Fan

Keep your space cool, fresh, and comfortable with the RS PRO Tower Fan. This whisper-quiet fan has 3-speed control settings that you can easily adjust using the remote control. The timer feature lets you set it for up to 8 hours. Get ready for some cool relief.

Features and Benefits

- Electrical control with touch button
- 3 speeds
- 8 hours timer
- With remote control

General Specifications

Air Flow	12.14 m ³ /min
Fan Type	Tower
Number of Speeds	3
Plug Type	Type G – British 3-pin
Supply Voltage	230 V
Dimensions	244.5 x 220 x 805.5 mm
Height	31.71in(80.55cm)
Special Features	Oscillating
Noise Level	<62dB(A)

Mechanical Specifications

Rated Voltage	230V
Rated Frequency	50Hz
Rating Power	44W
Airflow	1800pm
Wind Speed	233.93 (m ³ /min)
Swinging Head Angle	70°

Tilt Angle	30°
G.W.	4.02kgs
N.W.	3.05kgs
Product Size	244.5 x 220 x 805.5 mm
Package Size	850 x 185 x 215 mm

Approvals

Certifications	CE (EMC and LVD)
Declaration	REACH DoC

Similar Products

Stock No.	Brand	Product Name	No of Speed	Timmer	Plug Type
0227903	RS PRO	Tower Fan	3 speeds	8 hours	Type G - British 3-pin
0227904	RS PRO	Tower Fan	3 speeds	8 hours	Type C - European Plug



