


**605E**
**Click-type torque wrenches with reversible ratchets for right-hand and left-hand tightening torque accuracy:  $\pm 6\%$** 

**UNI EN ISO 6789**


Art. No.	art.	Nm	Kgfm	lbf.in	■	A mm	L mm	Wt g	Accuracy
<b>006050105</b>	605E/5	1÷5	0,1÷0,5	10÷45	1/4	20	190	180	0,05
<b>006050110</b>	605E/10	2÷10	0,2÷1,0	18÷90	1/4	20	190	180	0,1