

Specifications for BMP51/53 Labelmaker Labels

Adhesive	Permanent Acrylic
Article No.	143271
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Black on White/Transparent
Finish	Matt
Order Reference	M-33-427
Printable Area - Height (mm)	25.40
Printable Area - Width (mm)	38.10
Printer Compatibility	BMP51; BMP53
Size - Height (mm)	101.60
Size - Width (mm)	38.10
Additional Information	Self-Laminating;Self-Extinguishing;Excellent water & oil resistance;Excellent abrasion and smudge resistance
Thickness (mm)	0.102
Total Qty per Pack	70 Label(s) / Box
Wire Gauge	3/0 to 400 kcmil
Approval/Compliance	UL Recognised
Application	Voice & Data Communication; Wire & Cable Marking
Industry	Data & Telecommunications;Electrical
Description	Our most popular wire & cable labels. Conformable material designed to adhere to highly curved surfaces, wires and cables. Features a white printable area with clear "tail" that wraps around marker. The clear tails serves as over-laminate to protect the text, providing superior resistance to abrasion, dirt, oils, solvents, water and excessive handling
Max. Service Temp. °C	60
Max. Wire/Cable Diameter (mm)	24.30
Min. Service	-80

Temp. °C	
Min. Wire/Cable Diameter (mm)	10.80
Shape	Rectangle
Software	LabelMark
Surface	For smooth & textured/rough surfaces
Voice/Data Application	50 Pair Copper;24 Pair Fibre;Backbone